

AUTOSTRIP CONCENTRATE

Direct Stencil Decoating Concentrate

DESCRIPTION

A range of concentrated stencil strippers for decoating direct stencils (PLUS emulsions and Capillex films).

Autostrip Concentrate offers easy storage and handling but must be mixed with the prescribed amount of water before use.

Autostrip Concentrate is available in four strengths:

Autostrip Concentrate 1:20
Autostrip Concentrate 1:25
Autostrip Concentrate 1:50
Autostrip Concentrate 1:60

Applications

Autostrip Concentrate has been formulated for removal of PLUS Emulsions and Capillex.

READ ENTIRE TECHNICAL DATA SHEET BEFORE USING THIS PRODUCT

FEATURES & BENEFITS

- Fast, effective stencil decoater concentrate for all direct stencils. Convenient concentrates make it economical and easy to mix. Compatible with the Brush Pump System. Contains no undissolved particles making it ideal for use in automatic cleaning machines.
- Convenient and economical, especially when used in conjunction with the Brush Pump System. Ideal for use with automatic machines.

WORKING INSTRUCTIONS

Mixing of Autostrip Concentrate

Mix 1 part Autostrip Concentrate as follows:

Autostrip Concentrate 1:20 - can be diluted with up to 20 parts cold water
Autostrip Concentrate 1:25 - can be diluted with up to 25 parts cold water
Autostrip Concentrate 1:50 - can be diluted with up to 50 parts cold water
Autostrip Concentrate 1:60 - can be diluted with up to 60 parts cold water



Use of Autostrip Solution

1. Remove all ink residues by applying Autosolve Screen Wash to both sides of the mesh and work in with a brush.
2. Wash both sides of mesh with water to remove all solvent traces.
3. With a brush, apply Autostrip liberally to both sides of the mesh.
4. Leave to stand for 3 to 5 minutes while the emulsion coating dissolves. Do not allow Autostrip to dry onto the screen as this will make the stencil difficult to remove.
5. Wash off the stencil with a strong spray followed by a high pressure gun.

For more information on how to use MacDermid Autotype products, go to the How to Guide section at macdermid.com/autotype.

SHELF LIFE & STORAGE

Autostrip Concentrate should be stored between 5 to 30 °C (40 to 86 °F). Do not freeze.

Shelf life at these conditions is two years.

PACKAGING

Autostrip Concentrate is available in trade packs of 6 x 1 Litres, 2 x 5 Litres, 1 x 25 Litre and 1 x 210 Litre.



SAFETY & WARNING

MacDermid Autotype recommends that the company/operator read and review the Safety Data Sheets for the appropriate health and safety warnings before use.

Safety Data Sheets are available from MacDermid Autotype.

WASTE TREATMENT

Prior to using any recommendations or suggestions by MacDermid Autotype for waste treatment, the user is required to know the appropriate local/state/federal regulations for on-site or off-site treatment which may require permits. If there is any conflict regarding our recommendations, local/state/federal regulations take precedent.

CONTACT INFORMATION

To confirm this is the most recent issue, please contact MacDermid Autotype
 salessupport@macdermidautotype.com

North America MacDermid Autotype Inc. 5210 Phillip Lee Drive Atlanta, GA 30336, USA (404) 696 4565 autotypeusinfo@macdermid.com	Europe MacDermid Autotype Ltd. Grove Road, Wantage, Oxon OX12 7BZ, UK +44 (0) 1235 771111 salessupport@macdermidautotype.com	Asia MacDermid Autotype Pte Ltd. No, 20 Tuas Avenue 6, Singapore, 639307 +65 689 79670 sginfo@autotype.com
---	--	--

Also read carefully warning and safety information on the Safety Data Sheet. This data sheet contains technical information required for safe and economical operation of this product.
 READ IT THOROUGHLY PRIOR TO PRODUCT USE.

DISCLAIMER: All statements, technical information and recommendations contained herein are based on tests we believe to be reliable, but the accuracy or completeness thereof is not guaranteed. No statement or recommendation shall constitute a representation unless set forth in an agreement signed by officers of seller and manufacturer. NO WARRANTY OR MERCHANTABILITY OR WARRANTY OF FITNESS FOR A PARTICULAR PURPOSE IS MADE. The following warranty is made in lieu of such warranties and all other warranties, express, implied, or statutory. Products are warranted to be free from defects in material and workmanship at the time sold. The sole obligation of seller and manufacturer under this warranty shall be to replace any product defective at the time sold. Under no circumstances shall manufacturer or seller be liable for any loss, damage or expense, direct or consequential, arising out of the inability to use the product. Notwithstanding the foregoing, if products are supplied in response to a customer request that specifies operating parameters beyond those stated above, or if products are used under conditions exceeding said parameters, the customer by acceptance or use thereof assumes all risk of product failure and of all direct, indirect and consequential damages that may result from use of the products under conditions, and agrees to exonerate, indemnify and hold harmless MacDermid Incorporated therefrom. No suggestion for product use nor anything contained herein shall be construed as a recommendation to use any product in infringement of any patent rights, and seller and manufacturer assume no responsibility or liability for any such infringement.

® Registered Trademark of MacDermid Performance Solutions. ™ Trademark of MacDermid Performance Solutions.
 © Platform Specialty Products Corporation and its subsidiaries 2016.

