

# CAPILLEX 30 Solvent Resistant Capillary Film

# DESCRIPTION

Capillex films are precision coated, pre-sensitised capillary photostencil films, which are adhered to the mesh with water prior to exposure.

The films are coated onto a  $75\mu$  (3 thou) polyester base. The films have been designed for use with solvent based or UV curing inks.

# Applications

A red photopolymer based capillary film for use on medium mesh counts.

- Medium format graphics
- Textile printing with plastisol inks

READ ENTIRE TECHNICAL DATA SHEET BEFORE USING THIS PRODUCT

# **FEATURES & BENEFITS**

- Capillex 30 is exceptionally easy to use. The fast exposure speed is perfect for use on large screens or with lower powered light sources. Can be used with all solvent and UV inks.
- Mesh range: 77 to 100/cm (195 to 250/inch).
- Very easy to use under a wide range of processing conditions.
- Short exposure times.
- Very quick to develop.
- Tough.
- Easy to decoat.

# WORKING INSTRUCTIONS

## Mesh Preparation

All new synthetic monofilament meshes should be abraded with Autoprep Gel before use. (Used meshes should be re-abraded after every 5 stencils).



All meshes should be degreased using Universal Mesh Prep immediately prior to mounting the film.

# Adhering to the Mesh

For large or small screens: -

For best results use the Caplicator film applicator. Cut the film to size and place the film on a dry, flat surface. Using the Autotype Anti-Static Duster, remove dust from the polyester as the film is rolled, emulsion side out, leaving approximately 2 cm (3/4 inch) unrolled. Place the film inside the Caplicator. Spray the mesh with water and wipe excess water from the perimeter of the frame to avoid rivulets after adhering the film.

Contact the rolled film leading edge onto the top of the wet vertical screen and unroll the film down the screen, thus adhering it to the mesh. Remove excess moisture from the inside of the screen with a lightweight, window cleaner type squeegee. Wipe excess water from the perimeter of the frame with absorbent cloth then proceed to drying.

For small screens only:-

Place the film emulsion side up onto a raised pad and lay the dry degreased screen on top. Using a hand spray water bottle, spray water onto the mesh until the film is completely wet. Then squeegee off excess water from the inside of the screen. Wipe water from the perimeter of the frame then proceed to drying.

For more information on how to apply Capillex film, go to the How to Guide section at macdermid.com/Autotype.

# **Drying the Screen**

The screen can be dried with cold or warm air, maximum 30 °C (86 °F). Thorough drying is essential for optimum results. When the support has been peeled off continue drying for a few minutes to ensure the film is completely dry.


### Storage of Screens

After applying the Capillex film to the screen and drying, the screens can be kept in the dark for up to a week before exposure, provided that ambient temperature and humidity conditions are maintained. If storage of screens is anticipated, it is recommended that the backing sheet is not removed until the screen is about to be exposed.

### Exposure

Correct exposure is essential for optimum stencil performance. Underexposure will give a weak stencil and reduce resistance.

Remove dust from the surface of the stencil and tape positive in position. Place entire screen in a suitable vacuum frame and expose. We recommend use of the Autotype Exposure Calculator for test exposures to ascertain correct timing.





# Washout & Drying

Wash out the screen from both sides with a strong spray of water. Continue the washout until all parts of the image appear clean and sharp. Blot off surplus moisture and dry at a maximum temperature of 30  $^{\circ}$ C (86  $^{\circ}$ F).

Spot out pinholes with sensitised emulsion.

## Blockout

Block out the area between the edge of the stencil and the frame with Regular, Thick or Blue Filler when using solvent based or UV curing inks.

#### Stencil Removal

Remove ink from the screen with an Autosolve screen cleaner. Then apply Autostrip to both sides of the screen and leave to stand for 5 minutes. The stencil can then be removed with a strong water jet. If a stain or ghost image still remains, use Autokleen Plus.

For more information on how to use MacDermid Autotype products, go to the How to Guide section at macdermid.com/autotype.

### **SHELF LIFE & STORAGE**

The film should be kept in the protective packaging supplied. Store in a cool place away from hot drying cupboards and radiators. Do not store in a damp place. Correct storage conditions are at a temperature of 5 to 20  $^{\circ}$ C (40 to 86  $^{\circ}$ F) and at a relative humidity of 45-60%.

Shelf life at these conditions is two years.

## PACKAGING

Capillex is available in roll widths of 61 cm, 104 cm and 122 cm wide (24 in, 41 in and 48 in) and in a variety of lengths. Custom cut sheets are available upon request.





## **SAFETY & WARNING**

MacDermid Autotype recommends that the company/operator read and review the Safety Data Sheets for the appropriate health and safety warnings before use.

Safety Data Sheets are available from MacDermid Autotype.

## WASTE TREATMENT

Prior to using any recommendations or suggestions by MacDermid Autotype for waste treatment, the user is required to know the appropriate local/state/federal regulations for onsite or off-site treatment which may require permits. If there is any conflict regarding our recommendations, local/state/federal regulations take precedent.

## **CONTACT INFORMATION**

### To confirm this is the most recent issue, please contact MacDermid Autotype

salessupport@macdermidautotype.com

North America MacDermid Autotype Inc. 5210 Phillip Lee Drive Atlanta, GA 30336, USA (404) 696 4565 autotypeusinfo@macdermid.com	Europe MacDermid Autotype Ltd. Grove Road, Wantage, Oxon OX12 7BZ, UK +44 (0) 1235 771111 salessupport@macdermidautotype.com	Asia MacDermid Autotype Pte Ltd. No, 20 Tuas Avenue 6, Singapore, 639307 +65 689 79670 sginfo@autotype.com	
autotypeusinfo@macdermid.com	salessupport@macdermidautotype.com	sginfo@autotype.com	

Also read carefully warning and safety information on the Safety Data Sheet. This data sheet contains technical information required for safe and economical operation of this product. READ IT THOROUGHLY PRIOR TO PRODUCT USE.

DISCLAIMER: All statements, technical information and recommendations contained herein are based on tests we believe to be reliable, but the accuracy or completeness thereof is not guaranteed. No statement or recommendation shall constitute a representation unless set forth in an agreement signed by officers of seller and manufacturer. NO WARRANTY OR MERCHANTABILITY OR WARRANTY OF FITNESS FOR A PARTICULAR PURPOSE IS MADE. The following warranty is made in lieu of such warranties and all other warranties, express, implied, or statutory. Products are warranted to be free from defects in material and workmanship at the isoslo. The sole obligation of seller and manufacturer under this warranty shall be to replace any product defective at the time sold. Under no circumstances shall manufacturer or seller be liable for any loss, damage or expense, direct or consequential, arising out of the inability to use the product. Notwithstanding the foregoing, if products are supplied in response to a customer request that specifies operating parameters beyond those stated above, or if products are used under conditions exceeding said parameters, the customer by acceptance or use thereof assumes all risk of product failure and of all direct, indirect, indirect and consequential damages that may result from use of the products under conditions, and agrees to exonerate, indemnify and hold harmless MacDermid Incorporated therefrom. No suggestion for product use nor anything contained herein shall be construed as a recommendation to use any product in infringement of any patent rights, and seller and manufacturer assume no responsibility or liability for any such infringement.

Registered Trademark of MacDermid Performance Solutions. 
™ Trademark of MacDermid Performance Solutions.
© Platform Specialty Products Corporation and its subsidiaries 2016.

